



Ad ISI Fine/Coarse Coil Driver Chassis
LIGO D0902744

Over Temp Fuse Status
F1 +5V
F2 +5V
F3 +5V
F4 +5V
F5 +5V
F6 +5V
F7 +5V
F8 +5V

LIGO EEIP

Interface Chassis LIGO-D1000067

Geophones 3&4

Interface Chassis LIGO-D1000067

LIGO EEIP

Anti-Alias Chassis LIGO-D1000269

In 25-28 In 29-32

DC Power +5V -5V

LIGO HAM ISI Anti-Alias Chassis LIGO-D1000269

Anti-Alias Chassis LIGO-D1100202

Out 9-12 Out 13-16

LIGO EEIP

Ad ISI Fine/Coarse Coil Driver Chassis
LIGO D0902744

Over Temp Fuse Status
F1 +5V
F2 +5V
F3 +5V
F4 +5V
F5 +5V
F6 +5V
F7 +5V
F8 +5V

Over Temp Reset

LIGO EEIP

Chassis LIGO-D1000272

In 1-5 In 6-10 In 11-15 In 16-20

DC Power +5V -5V

In 21-26 In 27-29 In 29-32

8 CHANNEL VALVE DRIVER
LIGO D0900117-v2

CHANS 555 CHANS 7&8

LIGO EEIP



Capacitive Position sensors

+15
-15
GO EEIP
No Electrical Hazard

Chassis

Anti-Alias Chassis

In 25-28

In 29-32

LIGO-D1000269

In 29-32

LIGO-D1100202

Out 9-12

Out 13-16

Over Temp Reset

Over Temp

29

28

27

6

5

4

3

2

1

LIGO-D1000269

LIGO-D1000269

LIGO EEIP

MT 002 0001 0017 0001

MT 002 0001 0017 0001

MT 002 0001 0017 0001

MT 002 0001 0017 0001

MT 002 0001 0017 0001

MT 002 0001 0017 0001

MT 002 0001 0017 0001